

# My World


High Definition Surfacing

## SWISSCOAT My World - iRelax<sup>3</sup>

With our **SWISSCOAT iRelax<sup>3</sup>**, wearers are now feeling less visual fatigue when reading or working with computers. With iRelax<sup>3</sup>, you can relax your eyes during working and it is designed and calculated for reducing a visual fatigue. People between 25 and 45 years old who needs to spend long time using the near vision, working with computers, and, as result of it, have visual fatigue, are ideal wearers for the **iRelax<sup>3</sup>**

- \* Full Vision range
- \* Wearer within 25 to 40 years
- \* There are two models provided: Rlx5 & Rlx7
- \* Spending few hours on reachable distance operation
- \* Reading and computer working
- \* High Definition surfacing
- \* Reduce and eliminate the visual fatigue
- \* High quality feature in near zone

**Standard requirement:**  
(Minimum frame height: 27mm)



Progressive engraving:


Temple

Nasal >




| iRelax <sup>3</sup> — Nasal Engraving XX / Supply Power Range (Add 0.50D & 0.750D) |       |                |                               |                                    |                                     |              |
|--|-------|----------------|-------------------------------|------------------------------------|-------------------------------------|--------------|
| Material   | Index | Clear          | Transitions<br>(Brown / Grey) | Transitions<br>XTRActive<br>(Grey) | Polarized<br>(Brown / Grey / Green) | Drivewear    |
| CR39   | 1.498 | <b>E</b>       | <b>T</b>                      | <b>T</b>                           | <b>Z</b>                            | <b>W</b>     |
|  |       | +8.50D~8.00D   | +6.50D~8.00D                  | +6.50D~8.00D                       | +6.50D~8.00D                        | +6.50D~8.00D |
| SAFEwear<br>by Trilogy   | 1.53  | <b>V</b>       | <b>TV</b>                     | <b>TV5</b>                         | <b>ZV</b>                           | -----        |
|  |       | +7.00D~8.00D   | +7.00D~8.00D                  | +7.00D~8.00D                       | +7.50D~8.00D                        |              |
| ACTIFwear  | 1.589 | <b>L</b>       | <b>TL</b>                     | -----                              | <b>ZL</b>                           | <b>WL</b>    |
|  |       | +8.00D~9.00D   | +8.00D~9.00D                  |                                    | +8.00D~9.00D                        | +7.00D~9.00D |
| 1.6<br>High Index  | 1.61  | <b>H</b>       | <b>TH</b>                     | <b>TH</b>                          | <b>ZH (Brown / Grey)</b>            | -----        |
|  |       | +7.50D~9.50D   | +10.00D~10.00D                | +10.00D~10.00D                     | +8.00D~10.00D                       |              |
| 1.67<br>High Index   | 1.67  | <b>P</b>       | <b>TP</b>                     | <b>TP</b>                          | <b>ZP (Brown / Grey)</b>            | -----        |
|  |       | +12.50D~11.00D | +10.00D~11.00D                | +10.00D~11.00D                     | +7.50D~11.00D                       |              |
| 1.74<br>High Index   | 1.74  | <b>U</b>       | <b>TU</b>                     | -----                              | -----                               | -----        |
|  |       | +11.00D~12.00D | +10.00D~13.00D                |                                    |                                     |              |

# Marking and Centration Chart



RIGHT LENS  
(Concave)



LEFT LENS  
(Concave)

